

# Steuerungen

## MultiSwitch TL, Two-Light TL, Jo-Adapter line TL

### Jo - Adapter line TL (Two-Light Technologie) 12 V DC

- Jo-Adapter line TL for fixed Color setting
- coded for LED lamp 12 volt DC

	electric main	electric main	length
76.19949.29	black	max. 36 W	250 mm




### MultiSwitch TL for Two-Light spot 12 V DC

By touching the MultiSwitch TL, the Two-Light Lamp series is continuously adjustable to personal color preference from warm white (2700 K) to cool white (6500 K).

- Primary cable 2000 mm with Jo plug
- Secondary cable 1000 mm with coupling
- For surface mounting

	finish	power
76.19157.29	black	max. 36.0 W



### i MultiSwitch TL Function

Apart from an on/off switch, the Multi-Switch TL also allows color regulation, which means that by touching the MultiSwitch TL, the lamp series TL is switched on or off and if touched for longer period, the color temperature is adjusted from warm white to cool white. The last adjusted value is memorized.

### Two-Light TL - Radio Control 12 V DC

Two-Light radio control serves warm white/cool white colortemperature control purposes for the two-color(Two-Light)lamp systems. The control unit can be used for the TL lamp series as well as for the LED Strips TL. The color temperature is simply selected with a rotating knob. The memory function memorizes the last adjusted value. The SET consists of a radio dimmer and radio receiver.

- Light color: Two-Light
- Receiver: cable 180 mm Jo-connection system
- Measures (l<sub>w</sub>xh): 87 mm x 50 mm x 10 mm
- Measures (l<sub>w</sub>xh): 80 mm40 mm15 mm

	finish	power	ampère
76.19262.11	white	max. 30.0 W	max. 2.5 A

### i Two-Light TL Function

- Switching the light on/off and dimming using the remote control unit
- Colour temperature adjustment via the rotating knob on the remote control unit
- The last adjusted light value memorized
- The Receiver should be installed at an accessible point
- Before using the Radio remote control unit for the first time, carefully read the Installation instructions and follow instructions accratly
- Accessories:
  - Order the power pack separatly (page A-1.20A-1.20).

